

Autumn cools down
& our savings heat up!

INSTANT REBATES

up to \$1,091

THESE
REBATES
GIVE ME A
BIG GRIN!



Promotion valid
10/1/25 –
12/31/25

UPS systems and accessories



Product	Rebate	Description
9PX online double-conversion UPS systems		
9PX11KG2	\$1,091.84	11000VA 11000W, 208V, 9PX G2, Hardwired Input, 4 L6-30R/Hardwired Output, Cybersecure Network Card, Extended Run, 4U Rack/Tower
9PX3000GRT-L	\$702.31	3000VA 2700W, 208V, Lithium-Ion Battery, L6-20P, 8 C13, 2 C19 Outlets, Cybersecure Network Card Option, 2U Rack/Tower
9PX6KIECG2	\$739.28	6000VA 5400W, 208V, 9PX G2, L6-30P or Hardwired Input, 6 C39 and 6 C13 Outlets, Cybersecure Network Card, Extended Run, 3U Rack/Tower
Tripp Lite series line-interactive UPS systems		
SU1000RTXLCD2U	\$128.70	1000VA 900W, 120V, Sine Wave Output, 8 Outlets, Extended Run, Network Card Option, LCD, USB, DB9, 2U Rack/Tower
SU1500RTXLCD2UTAA	\$182.60	1500VA 1350W, 120V, Sine Wave Output, 8 Outlets, Extended Run, Network Card Option, LCD, USB, DB9, 2U Rack/Tower, TAA
SU2200RTXLCD2UTAA	\$275.00	2000VA 1800W, 120V Sine Wave Output, 7 5-15R Outlets, Network Card Option, 2U Rack/Tower, TAA
SU3000RTXLCD2UTAA	\$353.20	3000VA 2700W, 120V, Sine Wave Output, 7 Outlets, Extended Run, Network Card Option, LCD, USB, DB9, 2U Rack/Tower, TAA
SU1000LCD2U	\$160.50	1000VA 900W, 208/230V, 6 C13 Outlets, C14 Input, Network Card Option, 2U Rack/Tower
SU1500LCD2U	\$154.05	1500VA 1350W, 208/230V, 8 Outlets, Extended Run, Network Card Option, LCD, USB, DB9, 2U Rack/Tower
SU12200LCD2U	\$239.80	2200VA 2000W, 208/230V, 10 Outlets, Extended Run, Network Card Option, LCD, USB, DB9, 2U Rack/Tower
Extended battery modules and UPS accessories		
BP48RT2UTAA	\$106.80	48V Extended Battery Module (EBM) for SmartOnline UPS Systems, 2U Rack/Tower, TAA
BP48V	\$92.40	48V Extended Battery Module (EBM) for SU1500XLCD SmartOnline UPS Systems, Tower
BP72RT2UTAA	\$113.33	72V Extended Battery Module (EBM) for SmartOnline UPS Systems, 2U Rack/Tower, TAA
CB1ADAPT180RT	\$13.42	Adapter Cable to Connect 9PX G1 UPS or EBM to 9PX G2 UPS or EBM (180V)
CB1ADAPT240RT	\$13.42	Adapter Cable to Connect 9PX G1 UPS, EBM or SC240RT to 9PX G2 UPS or EBM (240V)
WMNTKIT	\$7.72	Wall-Mount Kit for Select 2U SmartPro, SmartOnline, 5PX G2 and 9PX UPS Systems and Extended Battery Modules

Network card



Product	Rebate	Description
NETWORK-M3	\$50.51	Eaton Cybersecure Gigabit NETWORK-M3 Card for Select Eaton UPSs and PDUs

Secure KVM switches



Product	Rebate	Description
B002-DP1A4-N4	\$115.00	4-Port, Single Head, DisplayPort to DisplayPort, 4K, NIAP PP4.0, Audio, TAA
B002-DP1AC4-N4	\$135.10	4-Port, Single Head, DisplayPort to DisplayPort, 4K, NIAP PP4.0, Audio, CAC, TAA
B002-DP2AC4-N4	\$155.20	4-Port, Dual Head, DisplayPort to DisplayPort, 4K, NIAP PP4.0, Audio, CAC, TAA
B002-DV2A4-N4	\$117.90	4-Port, Dual Head, DVI to DVI, NIAP PP4.0, Audio, TAA
B002-DV2AC4-N4	\$135.10	4-Port, Dual Head, DVI to DVI, NIAP PP4.0, Audio, CAC, TAA
B002-HD1AC4-N4	\$117.90	4-Port, Single Head, DP to HDMI (x4), 4K, NIAP PP4.0, Audio, CAC, TAA

Rebates apply only to items in stock during the promotional period. Excludes CDW, Amazon (US & Canada), Provantage and Staples.

3-phase managed PDUs



Product	Rebate	Description
EMAGECA5A2A5A2L	\$628.88	HDX Rack PDU G4, 240/415V, 54 Outlets (42 C13 + 12 C39), 64A, 46kW, Hardwired Input, 0U Vertical, TAA
EMAGECA5A5A5A5L	\$628.88	HDX Rack PDU G4, 240/415V, 48 Outlets (24 C13 + 24 C39), 64A, 46kW, Hardwired Input, 0U Vertical, TAA
EMAGECC2C2C2C2L	\$648.38	HDX Rack PDU G4, 240/415V, 48 C13 Outlets, 64A, 46kW, Hardwired Input, 0U Vertical, TAA
EMAGECC3C3C3C3L	\$587.44	HDX Rack PDU G4, 240/415V, 36 Outlets (24 C13 + 12 C39), 64A, 46kW, Hardwired Input, 0U Vertical, TAA
EMAGECC4C4C4C4L	\$552.92	HDX Rack PDU G4, 240/415V, 24 C39 Outlets, 64A, 46kW, Hardwired Input, 0U Vertical, TAA
EMAGFFA5A2A5A2L	\$692.25	HDX Rack PDU G4, 240/415V, 54 Outlets (42 C13 + 12 C39), 60A, 35kW, 560P6W Input, 6 ft. Cord, 0U Vertical, TAA
EMAGFFC2C2C2C2L	\$672.75	HDX Rack PDU G4, 240/415V, 48 C13 Outlets, 60A, 35kW, 560P6W Input, 6 ft. Cord, 0U Vertical, TAA
EMAGFFC3C3C3C3L	\$636.19	HDX Rack PDU G4, 240/415V, 36 Outlets (24 C13 + 12 C39), 60A, 35kW, 560P6W Input, 6 ft. Cord, 0U Vertical, TAA
EMAGFFC4C4C4C4L	\$604.50	HDX Rack PDU G4, 240/415V, 24 C39 Outlets, 60A, 35kW, 560P6W Input, 6 ft. Cord, 0U Vertical, TAA
EMAGKEA4A4A4A4L	\$594.75	HDX Rack PDU G4, 208V, 48 Outlets (24 C13 + 24 C19), 100A, 36kW, Hardwired Input, 0U Vertical, TAA
EMAGKEA5A2A5A2L	\$606.94	HDX Rack PDU G4, 208V, 54 Outlets (42 C13 + 12 C39), 100A, 36kW, Hardwired Input, 0U Vertical, TAA
EMAGKEA5A5A5A5L	\$599.63	HDX Rack PDU G4, 208V, 48 Outlets (24 C13 + 24 C39), 100A, 36kW, Hardwired Input, 0U Vertical, TAA
EMAGKEC2C2C2C2L	\$609.38	HDX Rack PDU G4, 208V, 48 C13 Outlets, 100A, 36kW, Hardwired Input, 0U Vertical, TAA
EMAGKEC3C3C3C3L	\$565.50	HDX Rack PDU G4, 208V, 36 Outlets (24 C13 + 12 C39), 100A, 36kW, Hardwired Input, 0U Vertical, TAA
EMAGKEC4C4C4C4L	\$552.92	HDX Rack PDU G4, 208V, 24 C39 Outlets, 100A, 36kW, Hardwired Input, 0U Vertical, TAA
EMAGLFA5A2A5A2L	\$613.76	HDX Rack PDU G4, 208V, 54 Outlets (42 C13 + 12 C39), 60A, 17kW, 460P9W Input, 6 ft. Cord, 0U Vertical, TAA
EMAGLFA5A5A5A5L	\$604.01	HDX Rack PDU G4, 208V, 48 Outlets (24 C13 + 24 C39), 60A, 17kW, 460P9W Input, 6 ft. Cord, 0U Vertical, TAA
EMAGLFC2C2C2C2L	\$692.25	HDX Rack PDU G4, 208V, 48 C13 Outlets, 60A, 17kW, 460P9W Input, 6 ft. Cord, 0U Vertical, TAA
EMAGLFC3C3C3C3L	\$563.06	HDX Rack PDU G4, 208V, 36 Outlets (24 C13 + 12 C39), 60A, 17kW, 460P9W Input, 6 ft. Cord, 0U Vertical, TAA
EMAGLFC4C4C4C4L	\$552.92	HDX Rack PDU G4, 208V, 24 C39 Outlets, 60A, 17kW, 460P9W Input, 6 ft. Cord, 0U Vertical, TAA
EMAGMFA5A2A5A2L	\$711.26	HDX Rack PDU G4, 208V, 54 Outlets (42 C13 + 12 C39), 80A, 29kW, 4100P9W Input, 6 ft. Cord, 0U Vertical, TAA
EMAGMFA5A5A5A5L	\$697.13	HDX Rack PDU G4, 208V, 48 Outlets (24 C13 + 24 C39), 80A, 29kW, 4100P9W Input, 6 ft. Cord, 0U Vertical, TAA
EMAGMFC2C2C2C2L	\$692.25	HDX Rack PDU G4, 208V, 48 C13 Outlets, 80A, 29kW, 4100P9W Input, 6 ft. Cord, 0U Vertical, TAA
EMAGMFC3C3C3C3L	\$670.31	HDX Rack PDU G4, 208V, 36 Outlets (24 C13 + 12 C39), 80A, 29kW, 4100P9W Input, 6 ft. Cord, 0U Vertical, TAA
EMAGMFC4C4C4C4L	\$648.38	HDX Rack PDU G4, 208V, 24 C39 Outlets, 80A, 29kW, 4100P9W Input, 6 ft. Cord, 0U Vertical, TAA

Surge protectors



Product	Rebate	Description
TLM609SA	\$5.09	Protect II! 6-Outlet Industrial Safety Surge Protector, 9 ft. Cord, 1500 Joules, Cord Wrap, Metal Housing
TLM615SA	\$5.80	Protect II! 6-Outlet Industrial Safety Surge Protector, 15 ft. Cord, 2700 Joules, Cord Wrap, Metal Housing
TLM704SA	\$1.83	Protect II! 7-Outlet Industrial Safety Surge Protector, 4 ft. Cord, 450 Joules, Metal Housing
TLM812SA	\$6.63	Protect II! 8-Outlet Industrial Safety Surge Protector, 12 ft. Cord, 1500 Joules, Cord Wrap, Metal Housing
TLM825USB	\$5.48	Protect II! 8-Outlet Industrial Safety Surge Protector, 2 USB-A Ports, 25 ft. Cord, 1960 Joules, Cord Wrap, Metal Housing
SS7619-15	\$9.75	24-Outlet Industrial Surge Protector, 15 ft. Cord, 1650 Joules, Metal Housing
TLP26PD30WCAM	\$5.85	Safe-IT 30W 2-Outlet Surge Protector, 3 USB Ports, 6 ft. Cord, 300 Joules, Antimicrobial Protection
TLP28PD57WCAM	\$7.13	Safe-IT 57W 2-Outlet Surge Protector, 3 USB Ports, 8 ft. Cord, 300 Joules, Antimicrobial Protection

See reverse for more solutions

For more information, contact:

tdsynnex@eaton.com
eatonus@tdsynnex.com

EATON
Powering Business Worldwide

TD SYNnex

Tripp Lite is now part of Eaton.

© 2025 Eaton. All rights reserved.

Connectivity

Product	Rebate	Description
Docking stations		
U442-DOCK2-S	\$5.97	USB-C Dock, Dual Display, 4K HDMI/mDP, VGA, USB 3.x (5Gbps), USB-A/C Hub, GbE, 60W PD Charging
MTB4-DOCK01A	\$26.30	Thunderbolt 4 Dock, 8K HDMI and Thunderbolt, USB-C and USB-A Ports, 2.5 GbE, 96W PD Charging
Hubs		
U360-004-MINI	\$3.24	4-Port Portable USB 3.x (5Gbps) Hub
U360-004-SLIM	\$2.05	4-Port Ultra-Slim Portable USB 3.x (5Gbps) Hub
U360-007-5A2C	\$6.38	7-Port USB-C Hub, USB 3.2 Gen 1 and USB 3.2 Gen 2, 5 USB-A and 2 USB-C Ports
U360-007-SW	\$4.50	7-Port USB-C Hub, USB 3.2 Gen 1 (5 Gbps) USB-A Ports with On/Off Buttons, Optional USB-A Adapter
AV cables		
P568-006	\$0.52	High-Speed HDMI Cable, Digital Video with Audio, UHD 4K (M/M), 6 ft. (1.83 m), Black
P580-003	\$0.93	DisplayPort Cable with Latching Connectors, 4K 60 Hz, M/M, Black, 3 ft.
P580-006	\$1.03	DisplayPort Cable with Latching Connectors, 4K 60 Hz, M/M, Black, 6 ft.
P580-006-V4	\$1.75	DisplayPort 1.4 Cable with Latching Connectors, 8K (M/M), Black, 6 ft.
P580-010	\$1.88	DisplayPort Cable with Latching Connectors, 4K 60 Hz (M/M), Black, 10 ft.
P580-015	\$3.33	DisplayPort Cable with Latching Connectors, 4K 60 Hz (M/M), Black, 15 ft.
P580F-000	\$18.50	DisplayPort Fiber Extender Terminations for MPO Fiber Optic Cable, 8K 60 Hz, 32.4 Gbps, LSZH, Up to 328 ft.
P582-006	\$1.33	DisplayPort to HDMI Adapter Cable (M/M), 6 ft., TAA
Adapters		
U209-006-RJ45-X	\$2.25	USB-A to RJ45 Serial Rollover Cable (M/M), Cisco Compatible, 250 Kbps, 6 ft.
U336-000-R	\$3.16	USB 3.0 to Gigabit Ethernet NIC Network Adapter, 10/100/1000 Mbps
U444-006-H	\$3.06	USB-C to HDMI Active Adapter Cable (M/M), 4K, 6 ft.
U444-06N-H4GU-C	\$12.56	USB-C Multiport Adapter, 4K HDMI, USB 3.x (5Gbps) Hub Port, GbE, 60W PD Charging, HDCP
U444-06N-H4GUC3	\$6.67	USB-C Multiport Adapter, 4K 60 Hz HDMI, USB 3.2 Gen 2 Hub Ports, GbE, 100W PD Charging, HDR, HDCP 2.2
U444-06N-H4MUC3	\$5.72	USB-C Multiport Adapter, 4K 60 Hz HDMI, USB 3.2 Gen 2 Hub Ports, Memory Card Slots, 100W PD Charging, HDR, HDCP 2.2
U444-06N-H4U3CS	\$5.24	USB-C Multiport Adapter, 4K 60 Hz HDMI, USB 3.2 Gen 2 Hub Ports, 100W PD Charging, HDR, HDCP 2.2
U444-06N-HDV4K6	\$4.20	USB-C Multiport Adapter (M/3xF) - 4K 60 Hz HDMI, DVI, VGA, HDCP, White
U444-06NHDV4K6B	\$4.20	USB-C Multiport Adapter (M/3xF) - 4K 60 Hz HDMI, DVI, VGA, HDCP, Black
USB chargers and accessories		
U280MS-2N1-WH2	\$4.45	USB-C Wall & Travel Charger with Apple Watch Pad, 30W, MFi Certified, Compact 1-Port Design, White
U264-001-AND	\$7.00	Wireless Android Auto Adapter for Vehicles, Android and Google Phone Compatible, Black
U264-001-APL	\$7.00	Wireless Apple CarPlay Adapter for Vehicles, Apple iPhone Compatible, Black

Power strips

Product	Rebate	Description
PS120406	\$7.40	4-Outlet Power Strip, 6 ft. Cord
PS240810	\$10.80	8-Outlet Power Strip, 10 ft. Cord
PS26PD32WCAM	\$6.30	Safe-IT 32W 2-Outlet Power Strip, 3 USB Ports, 6 ft. Cord, Antimicrobial Protection
PS-602-HG	\$6.15	Medical-Grade Power Strip for Use Outside of Patient Care Vicinities, UL 1363, 6 Hospital-Grade Outlets, Antimicrobial Protection, 1.5 ft. Cord, TAA
PS-606-HG	\$12.45	Medical-Grade Power Strip for Use Outside of Patient Care Vicinities, UL 1363, 6 Hospital-Grade Outlets, Antimicrobial Protection, 6 ft. Cord
PS-607-HG-OEM	\$13.50	Medical-Grade Power Strip for Patient-Care Vicinities, UL 1363A, 6 Hospital-Grade Outlets, Safety Covers, 7 ft. Cord
PS-615-HG-OEM	\$13.28	Medical-Grade Power Strip for Patient-Care Vicinities, UL 1363A, 6 Hospital-Grade Outlets, Safety Covers, 15 ft. Cord

Rebates apply only to items in stock during the promotional period. Excludes CDW, Amazon (US & Canada), Provantage and Staples.



For more information, contact:

tdsynnex@eaton.com
eatonus@tdsynnex.com

Tripp Lite is now part of Eaton.

© 2025 Eaton. All rights reserved.

Product	Rebate	Description
Power cords		
P005-E06-6	\$16.67	C13 to P-Lock C14, Heavy-Duty, 15A, 250V, 14 AWG, 6 ft., Black, 6 Pack
P005-E06-ABL-6	\$16.67	C13 to P-Lock C14, 15A, 250V, 14 AWG, 6 ft., Blue, 6 Pack
P005-E06-ARD-6	\$16.67	C13 to P-Lock C14, 15A, 250V, 14 AWG, 6 ft., Red, 6 Pack
P007-010	\$1.07	5-15P to C13, - Heavy-Duty, 15A, 125V, 14 AWG, 10 ft., Black
P018-006	\$2.27	C14 to C15, Heavy-Duty, 15A, 250V, 14 AWG, 6 ft., Black
P018-E06-6	\$7.70	C15 to P-Lock C14, Heavy-Duty, 15A, 250V, 14 AWG, 6 ft., Black, 6 Pack
P018-E06-ABL-6	\$15.88	C15 to P-Lock C14, 15A, 250V, 14 AWG, 6 ft., Blue, 6 Pack
P018-E06-ARD-6	\$15.88	C15 to P-Lock C14, 15A, 250V, 14 AWG, 6 ft., Red, 6 Pack
P036-E06-6	\$26.67	C19 to P-Lock C20, Heavy-Duty, 20A, 250V, 12 AWG, 6 ft., Black, 6 Pack
P036-E06-ABL-6	\$26.67	C19 to P-Lock C20, 20A, 250V, 12 AWG, 6 ft. (1.8 m), Blue, 6 Pack
P036-E06-ARD-6	\$26.67	C19 to P-Lock C20, 20A, 250V, 12 AWG, 6 ft. (1.8 m), Red, 6 Pack
Fiber transceivers		
N286-01G-SX-C	\$9.77	Cisco-Compatible GLC-SX-MMD SFP Transceiver - 1000Base-SX, LC Duplex MMF, 1.25 Gbps, 850 nm, 1804 ft.
N286-01G-SX-G	\$9.77	SFP Transceiver - 1000Base-SX, LC Duplex MMF, 1.25 Gbps, 850 nm, 51804 ft.
N286-100G-SR4SA	\$74.91	Arista-Compatible QSFP-100G-SR4 QSFP28 Transceiver - 100GBase-SR4, MTP/MPO MMF, 100 Gbps, 850 nm, 328 ft.
N286-100G-SR4SC	\$74.91	Cisco-Compatible QSFP-100G-SR4-S QSFP28 Transceiver - 100GBase-SR4, MTP/MPO MMF, 100 Gbps, 850 nm, 328 ft.
N286-100G-SR4SG	\$74.91	QSFP28 Transceiver - 100GBase-SR4, MTP/MPO MMF, 100 Gbps, 850 nm, 328 ft.
N286-10G-SR-A	\$5.73	Arista-Compatible SFP-10G-SR SFP+ Transceiver - 10GBase-SR, LC Duplex MMF, 10 Gbps, 850 nm, 1312 ft.
N286-10G-SR-C	\$5.73	Cisco-Compatible SFP-10G-SR SFP+ Transceiver - 10GBase-SR, LC Duplex MMF, 10 Gbps, 850 nm, 1312 ft.
N286-10G-SR-G	\$5.73	SFP+ Transceiver - 10GBase-SR, LC Duplex MMF, 10 Gbps, 850 nm, 1312 ft.
N286-25G-SRS-G	\$42.81	SFP28 Transceiver - 25GBase-SR, LC Duplex MMF, 25 Gbps, 850 nm, 328 ft.
N286-40G-ESR4-A	\$55.38	Arista-Compatible QSFP-40G-SR4 QSFP+ Transceiver - 40GBase-SR4, MTP/MPO MMF, 40 Gbps, 850 nm, 1312 ft.
N286-40G-ESR4-C	\$55.38	Cisco-Compatible QSFP-40G-SR4 QSFP+ Transceiver - 40GBase-SR4, MTP/MPO MMF, 40 Gbps, 850 nm, 1312 ft.
N286-40G-ESR4-G	\$55.38	QSFP-40G-SR4 QSFP+ Transceiver - 40GBase-SR4, MTP/MPO MMF, 40 Gbps, 850 nm, 1312 ft.
Media converters		
N784-MDC-1STST	\$18.50	100 Mb ST to 100 Mb ST Mode Converter - 1310 nm Compatible, Up to 6.2 mi.
N784-MDC-4SCSC	\$19.50	100 Mb SC to 100 Mb SC Mode Converter - 1310 nm Compatible, Up to 24.9 mi.
N784-MDC-4STST	\$24.00	100 Mb ST to 100 Mb ST Mode Converter - 1310 nm Compatible, Up to 24.9 mi.
N784-MDC-6SCSC	\$25.00	100 Mb SC to 100 Mb SC Mode Converter - 1310 nm Compatible, Up to 37.3 mi.
N785-MDC-1SCSC	\$27.50	1 Gb SC to 1 Gb SC Gigabit Mode Converter - 850 nm and 1310 nm Compatible, 6.2 mi.
N786-001-SFP	\$32.50	10 Gb SFP+ to RJ45 Ethernet Media Converter - 850 nm and 1310 nm Compatible, 50 mi.
N786-MDC-SFSPFP	\$65.00	10 Gb SFP+ to 10 Gb SFP+ Mode Converter - 1310 nm and 1550 nm Compatible, 50 mi.

Display mounts and risers

Product	Rebate	Description
Tablet mounts		
DMTB911	\$6.68	Secure Desk or Wall Mount for 9.7 in. to 11 in. Tablets
DMTBD413	\$3.72	Full-Motion Flexible Long-Arm Desktop Mount for 4.7 to 12.9 in. Smartphones and Tablets
Monitor risers		
MR159D	\$3.37	Height Adjustable with Storage Drawer, Metal
MR2208G	\$5.58	Universal Glass-Top Riser
MR229USB	\$14.29	Wood Top Riser with USB-A Charging and Data Ports
MR248USBG	\$12.48	Height Adjustable with Glass Top, USB Ports and Audio Ports
WWSSC2414TAA	\$18.00	Desk-Clamp Riser with Storage Drawer, TAA

Workstations

Product	Rebate	Description
WWSS1332C	\$77.70	WorkWise Clamp-On Desk-Mounted Workstation, Single 13" to 32" Flat-Screen Display
WWSS1DWSTAA	\$156.80	Mobile Workstation with Monitor Arm, Casters, Locking Drawer, TAA
WWSS2DWSTAA	\$173.80	Mobile Workstation with 2 Adjustable Shelves, 2 Metal Drawers, Casters, TAA
WWSSDTAM	\$44.46	Safe-IT Adjustable-Height Sit-Stand Desktop Workstation, Antimicrobial Protection
WWSSRSTAA	\$131.40	Mobile Workstation with Adjustable Shelves, Locking Casters, TAA



25-09-115