

# UPS Quick Reference Guide

From desktop to data center, get the reliable power protection you need for your mission-critical equipment.

## ENTERPRISE UPS SOLUTIONS

### SmartPro® UPS Systems

#### Protect Servers & Network Equipment

- Remote management, Emergency Power Off (EPO), environmental monitoring, controllable load bank and external battery options
- Up to 4 communication ports work with PowerAlert® software to provide complete network power monitoring and management



Model	Outlets + Ports	Half-Load Runtime*	Comparable APC Model
<b>Tower UPS Systems</b>			
SMART750TSU	8+USB+DB9	13 min.	SUA750US
SMART1500	6+USB+DB9	20 min.	SMT1500
SMART2200NET	6+(3) DB9	27+ min.	SMT2200
<b>Rack-Mount UPS Systems</b>			
SMART750RM1UN	6+USB+DB9	13.2 min.	SMT750R2-NMC
SMART1000RM1UN	6+USB+DB9	14 min.	SMT750R2-NMC
SMART1000RMXL2U	8+USB+DB9	18 min.	SMX1000
SMART1500RMXL2U	8+USB+DB9	14+ min.	SUA1500RM2U
SMART2200RMXL2U	8+USB+DB9	12+ min.	SU2200RMXL3U
SMART5000RT3U	14+(2) USB+(2) DB9	38+ min.	SUA5000RMT5U

### SmartOnline® Single-Phase UPS Systems

#### Protect Servers, VoIP/Telecom & All Mission-Critical Equipment

- Continuous on-line, double-conversion operation with pure sine wave output and zero transfer time provides the highest level of protection available
- Communication ports and SNMP slot work with PowerAlert software to provide network power monitoring and management with remote management options
- Hot-swappable models<sup>(†)</sup> feature modular design with manual bypass switch and detachable PDU to allow zero-downtime power module/battery replacement
- Economy Mode setting reduces energy costs by operating at up to 97% power efficiency



Model	Outlets + Ports	Half-Load Runtime*	Comparable APC Model
<b>Tower UPS Systems</b>			
SU750XL	6+tel/Ethernet+USB+DB9	11+ min.	SMT750
SU1500XL	6+tel/Ethernet+USB+DB9	14+ min.	SURTA1500XL
SU2200XLa	7+tel/Ethernet+USB+DB9	14+ min.	SURTA2000XL
<b>Rack-Mount UPS Systems</b>			
SU750RTL2U	6+tel/Ethernet+USB+DB9	11+ min.	SUA750RM2U
SU1000RTL2UN	6+tel/DSL+USB+DB9	14+ min.	SRT1000RMXLA
SU2200RTL2CD2U	7+tel/DSL+USB+DB9	12+ min.	SURTA2200RMXL2U
SU3000RTL3U	9+tel/Ethernet+USB+DB9	14+ min.	SURTA3000RMXL3U
SU5000RT4UHV	4+USB+DB9	11+ min.	SURTD5000RMXL3U
SU10000RT3U <sup>†</sup>	6+USB+(2) DB9	12.5+ min.	SURT10000RMXL6U
SU16000RT4U <sup>†</sup>	13+Hardwire+USB+DB9	12+ min.	SYA16K16RMP

## DESKTOP UPS SOLUTIONS

### Digital LCD UPS Systems

#### Protect PCs, Small Servers & Audio/Video Systems

- Rotatable LCD screen shows a variety of operating conditions in real time
- Automatic voltage regulation (AVR) corrects brownouts and overvoltages without consuming battery power
- USB/DB9 ports work with FREE PowerAlert software (Web download) to provide automatic unattended shutdown
- 3-year product warranty



Model	Outlets + Ports	Half-Load Runtime*	Comparable APC Model
OMNI700LCDT	6+USB+tel/DSL	10 min.	BR700G
OMNI900LCD	8+USB	10 min.	BR1000G
OMNI1500LCDT	10+tel/DSL+coax	7.5 min.	BR1500G
SMART1000LCD	8+tel/DSL+coax+USB	10 min.	BR1000G
SMART1200LCD	8+tel/ Ethernet+USB+DB9	12 min.	BR1300G
SMART1500LCD	8+tel/ Ethernet+USB+DB9	11.8 min.	BR1500G
SMART1500LCDXL	8+tel/ Ethernet+USB+DB9	12+ min.	BR1500G

\*Based on single PC load with 15" flat-panel monitor. Runtimes may vary based on battery load and condition. + Models feature expandable runtime with optional external battery packs. †Audible alarm is completely muted from factory; can be restored using PowerAlert software.

See Reverse for More Desktop UPS Solutions

**TRIPP-LITE**  
by **EATON**

Tripp Lite is now part of Eaton.

For more information, contact your Eaton sales representative or visit

[tripplite.eaton.com](http://tripplite.eaton.com)

© 2023 Eaton. All rights reserved.

# UPS Quick Reference Guide

From desktop to data center, get the reliable power protection you need for your mission-critical equipment.

## DESKTOP UPS SOLUTIONS (continued)

### VS/AVR UPS Systems

#### Protect PCs, Workstations & Small Servers

- Automatic voltage regulation (AVR) corrects brownouts and overvoltages without consuming battery power
- USB/DB9 ports work with FREE PowerAlert software (Web download) to provide automatic unattended shutdown
- 3-year product warranty



UP TO  
\$250,000  
ULTIMATE  
Lifetime Insurance

Model	Outlets + Ports	Half-Load Runtime*	Comparable APC Model
<b>Flatpack UPS Systems</b>			
AVR550U	8+tel/DSL+USB	9 min.	N/A
AVR700U	8+tel/DSL+USB	10 min.	N/A
AVR900U	12+tel/DSL+USB	10 min.	N/A
<b>Tower UPS Systems</b>			
SMART550USB	6+tel/DSL/Ethernet+USB	14.8 min.	SC420
SMART750USB	6+tel/DSL/Ethernet+USB	8.3 min.	SC620
OMNIVS800	7+tel/DSL/Ethernet+USB	11.5 min.	BR1000G
OMNIVS1000	8+tel/DSL/Ethernet+USB	14 min.	BR1300G

### Lithium Battery UPS Systems

#### Enjoy Longer-Lasting, Faster-Recharging Protection

Lithium iron phosphate (LiFePO4) batteries:

- Charge to 100% capacity in about 1.5 hours
- Double the UPS service life vs. comparable lead-acid batteries
- Operate more effectively in extreme temperatures than typical lead-acid batteries
- Weigh approximately 60% less than lead-acid batteries



Model	Outlets + Ports	Half-Load Runtime*
SMART1000RM2UL	6+USB+DB9	20 min.
SMART1500RM2UL	8+USB+DB9	15.4 min.
SMART2200RM2UL	8+USB+DB9	11.7 min.
SMART3000RM2UL	9+USB+DB9	9.5 min.
SMART700HGL	4+USB+DB9	42 min.
SMART1200XLHGL	4+USB+DB9	28 min.

### Internet Office® UPS Systems

#### Protect PCs, Modems & All Peripherals

- Built-in, surge and line noise protection; tel/DSL surge protection (most models)
- USB/DB9 ports work with FREE PowerAlert software (Web download) to provide automatic unattended shutdown (most models)
- 3-year product warranty



Model	Outlets + Ports	Half-Load Runtime*	Comparable APC Model
BC350	6	7 min.	BE350G
INTERNET350SER	6+tel/DSL/Ethernet+DB9	7 min.	BE350G
INTERNET350U	6+tel/DSL/Ethernet+USB	7 min.	BE350G
INTERNET550SER	8+tel/DSL/Ethernet+DB9	5 min.	BE550G
INTERNET550U	8+tel/DSL/Ethernet+USB	5 min.	BE550G
INTERNET600U	8+tel/DSL/Ethernet+USB	4.5 min.	BE550G
INTERNET750U	12+tel/DSL/Ethernet+USB	8.6 min.	BE750G
INTERNET900U	12+tel/DSL/Ethernet+USB	7.8 min.	BE750G



ENERGY STAR® Certified

\*Based on single PC load with 15" flat-panel monitor. Runtimes may vary based on battery load and condition. + Models feature expandable runtime with optional external battery packs. †Audible alarm is completely muted from factory; can be restored using PowerAlert software.

For more information, contact your Eaton TD SYNEX sales representative:

seeaton@tdsynex.com  
triplite@tdsynex.com  
tdsynex@eaton.com

**TRIPP-LITE**  
by **EATON**

Tripp Lite is now part of Eaton.

