



Eaton 9PX lithium-ion UPS

Double conversion UPS that offers a set-it-and forget-it deployment

The 9PX lithium-ion UPS is part of the Eaton 9 series single-phase double conversion UPS line, best applied to mission-critical equipment for constant power conditioning. The 9PX lithium-ion UPS provides 8–10 years of life expectancy for UPS and batteries, and has power ratings varying from 1–3 kVA, with low and high voltage options, while also offering up to four external battery modules (EBM) for extra runtime. The 9PX lithium-ion UPS has the same reliable features as the lead-acid UPS: load segments allow for prioritized shutdown, remote power on (RPO), remote on/off (ROO) and output relay ports that increase control capabilities. For connectivity and enhanced UL and IEC cybersecurity, the Eaton Gigabit Network Card is compatible and is offered as an optional bundle.



For even more runtime, add up to four EBMs to your UPS



Key features and benefits

Save money

- **2-3X longer battery life:** minimize battery maintenance expense—ideal for large deployments and edge applications
- **Runtime:** lithium-ion UPS provides 80–120% more runtime at full load compared to lead-acid batteries
- **Warranty:** 5-year all-inclusive (electronics and battery) warranty

Save space

- **1U lithium EBM vs 2U lead-acid EBM**
- **Lightweight design** 40% less weight than a comparable lead-acid UPS allowing easier installation and saving time

Reduce risk

- **24/7 monitoring:** battery management system (BMS) improves reliability and performance by actively monitoring temperature and charge
- **Cybersecure:** remote monitoring service and network connectivity card options provide cybersecurity protection and keep you connected with your UPS status updates
- **On-board BMS monitoring** in combination with proven Lithium Iron Phosphate (LFP) chemistry provides a reliable and safe offering, giving you peace of mind

IPM – Intelligent Power Manager

The power of automation.

IPM is an easy-to-use disaster avoidance platform with sophisticated capabilities that include triggering alerts and automating resolutions to keep applications running. IPM enables you to:

- Leverage Eaton’s integrations with industry leaders to keep critical applications running and automate resolutions for your entire network risking potential downtime.
- Migrate workloads to increase system uptime and minimize generator load by suspending non-critical virtual machines.
- Power cap servers to keep critical loads running longer by limiting server power consumption.

Learn more at Eaton.com/IPM

VPM – Visual Power Manager

The power of monitoring.

With Visual Power Manager (VPM), you can remotely monitor the power of thousands of PDU and UPS devices through a user-friendly, visual interface that simplifies data for quick action. VPM enables you to:

- Gain vendor agnostic insight. Monitor a mixed environment through VPM’s unique protocol-based data collection.
- Know what’s coming. Analyze power devices visually and get notified ahead of replacement through custom reports.
- Get real-time, rack-level statistics. Quickly remediate through up-to-the-minute analytics, notifications and alarms for events exceeding what any branch can support.

Learn more at Eaton.com/VPM

PredictPulse™ Insight

The power of predictability.


PredictPulse Insight is the industry’s first cloud-based 24x7 remote monitoring and predictive analytics subscription service to forecast data center power component failure and proactively replace components before failure. PredictPulse enables you to:

- **Save time.** Focus on other critical IT tasks while this predictive analytics service and Eaton’s remote monitoring team oversees power remotely.
- **Save money.** Eliminate surprise maintenance expenses — this subscription-based service includes parts, labor, on-going preventive maintenance and expedited repairs.
- **Reduce risk.** Utilize Eaton’s proprietary algorithms, based on data from thousands of installed devices to predict UPS component failure and proactively replace parts before issues arise.

Learn more at Eaton.com/PredictPulse


Rear panel overview

Model 9PX1500RT-L




- | | | |
|---|---|-------------------------------------|
| 1 Output relay port | 5 EBM connector | 9 (2) 5-15R (load segment group 1) |
| 2 Remote power off (RPO) and remote on/off (ROO) port | 6 RS-232 serial communication port (cable included) | 10 (2) 5-15R (load segment group 2) |
| 3 External battery module (EBM) detection port | 7 USB port (cable included) | 11 Ground bonding screw |
| 4 Network Card-M2 (optional) | 8 (2) 5-15R managed outlets (primary group) | 12 8-foot line cord with 5-15P |

Model 9PX2200GRT-L and 9PX3000GRT-L



- | | | |
|---|---|---|
| 1 Output relay port | 6 RS-232 serial communication port (cable included) | 10 (1) C19 and (2) C13 managed outlets (load segment group 1) |
| 2 Remote power off (RPO) and remote on/off (ROO) port | 7 USB port (cable included) | 11 (2) C13 managed outlets (load segment group 2) |
| 3 External battery module (EBM) detection port | 8 (1) C19 outlet | 12 Ground bonding screw |
| 4 Network Card-M2 (optional) | 9 (4) C13 managed outlets (primary group) | 13 C20/L6-20P input connection (detachable L6-20P to C19 input cord is 6-feet long) |
| 5 EBM connector | | |

Model : 9PX3000RT-L



- | | | |
|---|--|---|
| 1 Output relay port | 6 RS-232 serial communication port (cable included) | 10 (2) 5-20R managed outlets (load segment group 2) |
| 2 Remote power off (RPO) and remote on/off (ROO) port | 7 USB port (cable included) | 11 Ground bonding screw |
| 3 External battery module (EBM) detection port | 8 (2) 5-20R and (1) L5-30R managed outlets (primary group) | 12 L5-30P input cord (8 feet long) |
| 4 Network Card-M2 (optional) | 9 (2) 5-20R managed outlets (load segment group 1) | 13 AC output branch protector |
| 5 EBM connector | | |

For additional rear panel views, please visit Eaton.com/9PX.

9PX lithium-ion rackmount and tower model selection guide*

The 9PX lithium-ion comes as a stand-alone UPS or as part of a network bundle for easy configuration and deployment. For complete specifications, including interactive battery runtime graphs, visit Eaton.com/9PX.

9PX- 120V (default), 100V, 110V, 115V, 125V RT models

Catalog number	Rating (VA/Watts)	Input connection	Output connection	Dimensions (H x W x D), in.	Rack size	Weight, lbs.
9PX1500RT-L	1500VA / 1350W	5-15P, 8 ft.	(8) 5-15R	3.41 x 17.32 x 17.72	2U	35.5
9PX2000RT-L	2000VA / 1800W	5-20P, 8 ft.	(1) L5-20R, (6) 5-20R	3.41 x 17.32 x 23.83	2U	50.6
9PX3000RT-L	3000VA / 2400W	5-30P, 8 ft.	(1) L5-30R, (6) 5-20R	3.41 x 17.32 x 23.83	2U	52.7

Global UPS, 208V (default), 230V, 240V RT models

Catalog number	Rating (VA/Watts)	Input connection	Output connection	Dimensions (H x W x D), in.	Rack size	Weight, lbs.
9PX1500GRT-L	1500VA / 1350W	C14	(8) C13	3.41 x 17.32 x 17.72	2U	34.8
9PX2200GRT-L	2200VA / 2000W	C20 / L6-20P	(8) C13, (2) C19	3.41 x 17.32 x 23.83	2U	48.6
9PX3000GRT-L	3000VA / 2400W	C20 / L6-20P	(8) C13, (2) C19	3.41 x 17.32 x 23.83	2U	50.2

9PX- 120V (default), 100V, 110V, 115V, 125V RT bundles

Catalog number	Description	Rating (VA/Watts)	Input connection	Output connection	Dimensions (H x W x D), in.	Rack size
9PX1500RTN-L	9PX 1500 120V RT w/ Network Card-M2	1500 / 1350	5-15P, 8 ft.	(8) 5-15R	3.41 x 17.32 x 17.72	2U
9PX2000RTN-L	9PX 2000 120V RT w/ Network Card-M2	2000 / 1800	5-20P, 8 ft.	(6) 5-20R, (1) L5-20R	3.41 x 17.32 x 23.83	2U
9PX3000RTN-L	9PX 3000 120V RT w/ Network Card-M2	3000 / 2400	L5-30P, 8 ft.	(6) 5-20R, (1) L5-30R	3.41 x 17.32 x 23.84	2U

9PX lithium-ion EBM options

Catalog number	Description	Rack size	Weight, lbs.
9PXEBM48RT-L	Extended battery module for 9PX1500RT-L and 9PX1500GRT-L	1U	36.5
9PXEBM72RT-L	Extended battery module for 9PX2000RT-L, 9PX2200GRT-L, 9PX3000RT-L and 9PX3000GRT-L	1U	46.6

9PX lithium-ion options

Power distribution (PDU) and maintenance bypass (MBP) options

Catalog	Description	Input connection	Output connection	Dimensions (H x W x D), in.
EHBPL1500R-PDU1U	HotSwap MBP for use with 9PX1500RT-L, 9PX1500GRT-L	5-15P	(6) 5-15R	2.1 (2U_ x 17.3 x 3.8
EHBPL2000R-PDU1U	HotSwap MBP for use with 9PX2000RT-L, 9PX2200GRT-L	5-20P	(6) 5-20R	2.1 (2U_ x 17.3 x 3.8
EHBPL3000R-PDU1U	HotSwap MBP for use with 9PX3000RT-L, 9PX3000GRT-L	L5-30P	(5) 5-20R	2.1 (2U_ x 17.3 x 3.8
ePBZ74	Basic 2 kVA, 120V, 0U ePDU	5-20P / L5-20P	(14) 5-20R	24 (0U) x 1.5 x 1.5
ePBZ78	Basic 3 kVA, 120V, 0U ePDU	L5-30P	(20) 5-20R	1.7 (1U) x 17 x 5.1
ePBZ88	Basic 2-3 kVA, 208V, 0U ePDU	C20	(10) C13, (2) C19	1.7 (1U) x 19 x 2.4
ePBZ93	Basic 3 kVA, 208V, 0U ePDU	L6-20P	(20) C13, (4) C19	35 (0U) x 1.9 x 2.4
ePBZ79	Basic 3-6 kVA, 120V, 1U ePDU	L6-30P	(16) C13, (4) C19	1.7 (1U) x 17 x 5.1

*For additional Eaton PDU options, please visit Eaton.com/RackPDUSelector

Catalog number	Description
NETWORK-M2	Gigabit Network Card
EMPDT1H1C2	Environmental Monitoring Probe (EMP) Gen 2 for use with Network-M2
RELAY-MS	Relay / Serial Interface Card

Mounting Hardware

RK2PA	1U two-post rail kit (optional)
RK2PC	2-post rack mounting rail kit (one kit required for each UPS and EBM)
BINTSYS	Battery integration – vertical mounting platform with wheels

*For additional Eaton PDU options, please visit Eaton.com/RackPDUSelector

Lithium-ion vs lead-acid

Characteristic	VRLA battery	Lithium-ion battery	Lithium-ion benefit
Average battery lifespan	3-5 years	8-10 years	2-3x longer life
Weight	43-86 lbs	34.8-52.7 lbs	20% lighter UPS, 40% lighter EBM
EBM Footprint	2U	1U	Increased U space for critical equipment
Warranty	2 years	5 years	2.5x warranty coverage
Battery replacement cost	\$650*	\$0	Reduced TCO

*Battery and labor cost for one replacement



2U UPS with 1U EBM in 4-post rack



Advanced control with IPM software allows for remote management and integration into leading virtualization platforms
Eaton.com/intelligentpower

To view battery runtimes and interact with the Eaton 9PX lithium-ion UPS,
please visit: Eaton.com/9PX

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2021 Eaton
All Rights Reserved
Printed in USA
Publication No. BR153145EN / GG
March 2021

Eaton, ABM, Intelligent Power Manager and
PredictPulse are registered trademarks.

All other trademarks are property
of their respective owners.

Follow us on social media to get the
latest product and support information.

